
# **IPF** ELECTRONIC

# KB32A112

# **CAPACITIVE SENSORS • NORM SWITCHING DISTANCE**

Capacitive proximity switches are contact-free sensors. They detect metallic and non-metallic objects, regardless of whether they move or not. The achievable sensing range of the devices depends on the object material, its dimensions and the response sensitivity, which is set via a potentiometer. The vibration-resistant sensors can be approached laterally or frontally. Capacitive proximity switches are used for presence detection (e.g. sealing detection), positioning (e.g. PET bottles), counting (e.g. plastic caps), level detection (e.g. lubricant) or distance measurements (e.g. thickness measurement) of solid and liquid materials.



### **MECHANICAL DATA**

Type of switching output

Active area material of sensor	PTFE
Ambient temperature	-25 °C 70 °C
Cable length	2 m
Degree of protection (IP)	IP67
Housing design	Cylinder, screw-thread
Housing material	Brass
Material of cable sheath	PVC
Mechanical mounting condition for sensor	Flush
Number of wires	3
Pressure-proof	No
Sensor length	70 mm
Thread pitch	1.5 mm
Thread size, metric	32
Wire cross section	0.75 mm²
ELECTRICAL DATA	
Cascadable	No
Max. output current	400 mA
No-load current	15 mA
Residual ripple	10 %
Reverse polarity protection	Yes
Setting procedure	Manual adjustment
Short-circuit-proof	Yes
Suitable for safety functions	No
Supply voltage	10 V 35 V
Switching distance	20 mm
Switching distance	2 mm 25 mm
Switching frequency	50 Hz
Type of electrical connection	Cable
Type of electrical connection Type of switching function	Cable Programmable/configurable

PNP/NPN



# **ELECTRICAL DATA**

Voltage drop	2 V
Voltage type	DC
With LED display	Yes
With monitoring function of downstream devices	No
OTHER DATA	
Level detection	Yes
Level detection of synthetic granules for injection molding	Yes

#### **DIMENSIONAL DRAWING**

# INSTALLATION



Mounting / Installation may only be carried out by a qualified electrician!

DISPOSAL



#### SAFETY WARNINGS

Before initial operation, please make sure to follow all safety instructions that may be provided in the product information!